

REBA 50 EXT LINE | REBA 65 EXT LINE

EN INSTALLATION INSTRUCTIONS

FR NOTICE DE MONTAGE

DE MONTAGEANLEITUNG

PT INSTRUÇÕES DE MONTAGEM

ES INSTRUCCIONES DE MONTAJE



IIV660



EN READ THE SUPPLEMENTARY MANUALS.

FR LIRE LES NOTICES DE MONTAGE SUPPLÉMENTAIRES.


DE LESEN SIE DIE ZUSÄTZLICHEN MONTAGEANLEITUNGEN

PT CONSULTE OS MANUAIS COMPLEMENTARES.

ES LEA LOS MANUALES COMPLEMENTARIOS.



IIV630 | IIV662 |
IIV881 | IIV966 |
IIV652 | IIV809 |
IIV910



Order code / Code com. / Bestell-Nr. / Código / Código: 90505... | 90509...



EN Carefully read the installation instructions provided before installing the device. Safety and Maintenance: Scan here. |

FR Lire attentivement les notices de montage avant l'installation de l'appareil. Sécurité et Entretien: Sancez ici. |


DE Bitte lesen die mitgelieferte Montageanleitungen vor de Montage des Geräts. Sicherheit und Wartung: Hier scannen. |





PT Leia atentamente as instruções de montagem fornecidas antes de instalar o aparelho. Segurança e Manutenção: Scan aqui. |





ES Lea atentamente las instrucciones de montaje proporcionadas antes de instalar el aparato. Seguridad y Mantenimiento: Escanea aqui. |



REBA 50 EXT Line | REBA 65 EXT Line



REBA 50 EXT Line			
START/END	MID	HORIZONTAL CORNER (HRZ)	VERTICAL CORNER (VRT)
 (mm)	 (mm)	 (mm)	 (mm)
567x50x72	562x50x72	601x601	606x606
847x50x72	842x50x72		
1127x50x72	1122x50x72		
1407x50x72	1402x50x72		
1687x50x72	1682x50x72		
1969x50x72	1964x50x72		
2249x50x72	2244x50x72		
2529x50x72	2524x50x72		
2809x50x72	2804x50x72		

REBA 65 EXT Line			
START/END	MID	HORIZONTAL CORNER (HRZ)	VERTICAL CORNER (VRT)
 (mm)	 (mm)	 (mm)	 (mm)
567x65x82	562x65x82	608x608	606x606
847x65x82	842x65x82		
1127x65x82	1122x65x82		
1407x65x82	1402x65x82		
1687x65x82	1682x65x82		
1969x65x82	1964x65x82		
2249x65x82	2244x65x82		
2529x65x82	2524x65x82		
2809x65x82	2804x65x82		

TOOLS | OUTILS | WERKZEUG | FERRAMENTAS | HERRAMIENTAS

Umbrako 2 mm
Phillips screwdriver




EN USE GLOVES.
FR UTILISEZ DES GANTS.
DE HANDSCHUHE BENUTZEN.
PT UTILIZE LUVAS.
ES USE GUANTES.



REBA 50 EXT Line

REBA 65 EXT Line


90505... | 90509...



or/ou/
oder/
ou/o **IIV662**
IIV910

START KIT KIT DÉBUT DE LIGNE START KIT START KIT START KIT

923100... | 923500...




THROUGH-WIRING
CÂBLAGE TRAVERSANT
DURCHGANGSVERDRÄHTUNG
CABLAGEM LINHA CONTÍNUA
CABLEADO PARA LÍNEA CONTÍNUA



IIV630


9456... | 9457... | 9480... | 9481... | 9482...



(x1)

BODY CONNECTOR KIT
KIT UNION
VERBINDUNGS KIT
KIT DE UNIÃO
KIT DE UNIÃO

932100 | 932200



(x2)


(x8)

(x2)

(x2)

BLANK PARTS
MODULE VIDE
BLINDMODUL
MÓDULOS CEGOS
MÓDULOS CEGOS


992900... | 992901...
 993000... | 993001...



(x1) 1500/3000mm

LIGHT CORNERS
ANGLES LUMINEUX
ECKLEUCHTE
CANTOS ILUMINADOS
ÂNGULOS ILUMINADOS

90505H... | 90505V...
 90509H... | 90509V...




(x1)

(x1)

S5 L1500 SUSPENSION
SUSPENSION S5 L1500
SEILABHÄNGUNG S5 L1500
SUSPENSÃO S5 L1500
SUSPENSIÓN S5 L1500

910408 | 910409



(x2/x1)



(x2/
x1)



(x2/
x1)



(x2/
x1)



(x2/
x1)




IIV652

**CEILING ROSE
PATÈRE DE SUSPENSION
DECKENDOSE
CAIXA DE ALIMENTAÇÃO
BASE DE TETO**



971400...


RECESSED CEILING ROSE - T7 Q90
PATÈRE DE SUSPENSION ENCASTRÉE - T7 Q90
DECKENDUSEN ZUM EINBAU - T7 Q90
CAIXA DE ALIMENTAÇÃO ENCASTRAR - T7 Q90
BASE DE TETO DE EMPOTRAR - T7 Q90



(x1) (x2/x4/x6) (x1) (x1)

978610...


SURFACE MOUNTED CEILING ROSE - T25 Q100
PATÈRE DE SUSPENSION SAILLIE - T25 Q90
DECKENDOSE ZUM ANBAU - T25 Q90
CAIXA DE ALIMENTAÇÃO SALIENTE - T25 Q90
BASE DE TETO DE SUPERFICIE - T25 Q90



(x2/x4/x6) (x1) (x1)

971410...


RECESSED CEILING ROSE - T59 Q100
PATÈRE DE SUSPENSION ENCASTRÉE - T59 Q100
DECKENDUSEN ZUM EINBAU - T59 Q100
CAIXA DE ALIMENTAÇÃO ENCASTRAR - T59 Q100
BASE DE TETO DE EMPOTRAR - T59 Q100



(x1) (x2/x4/x6) (x1) (x1)

978611...

SURFACE MOUNTED CEILING ROSE - T29 Q100
PATÈRE DE SUSPENSION SAILLIE - T29 Q100
DECKENDOSE ZUM ANBAU - T29 Q100
CAIXA DE ALIMENTAÇÃO SALIENTE - T29 Q100
BASE DE TETO DE SUPERFICIE - T29 Q100




(x2/x4/x6) (x1) (x1)

CEILING ROSE
PATÈRE DE SUSPENSION
DECKENDOSE
CAIXA DE ALIMENTAÇÃO
BASE DE TETO




971300...

RECESSED CEILING ROSE T5 D90
PATÈRE DE SUSPENSION ENCASTRÉE T5 D90
DECKENDOSE ZUM EINBAU T5 D90
CAIXA DE ALIMENTAÇÃO ENCASTRAR T5 D90
BASE DE TETO DE EMPOTRART T5 D90




978700...




979000...


SURFACE MOUNTED CEILING ROSE T64 D85
PATÈRE DE SUSPENSION SAILLIÉ T64 D85
DECKENDOSE ZUM ANBAU T64 D85
CAIXA DE ALIMENTAÇÃO SALIENTE T64 D85
BASE DE TETO DE SUPERFICIE T64 D85



979003...

SURFACE MOUNTED CEILING ROSE T69 D85
PATÈRE DE SUSPENSION SAILLIÉ T69 D85
DECKENDOSE ZUM ANBAU T69 D85
CAIXA DE ALIMENTAÇÃO SALIENTE T69 D85
BASE DE TETO DE SUPERFICIE T69 D85




 Dimensions do not include start kit. To complete the line add 6 mm to the length.

LINE (TOP VIEW)

REBA 50 EXT LINE				
L/L1	A	B	C	E
567/562		422		
847/842		702		
1127/1122		982		
1407/1402		1262		
1687/1682	75	1542	140	46
1969/1964		1824		
2249/2244		2104		
2529/2524		2384		
2809/2804		2664		

LINE (TOP VIEW)


REBA 65 EXT LINE				
L/L1	A	B	C	E
567/562		422		
847/842		702		
1127/1122		982		
1407/1402		1262		
1687/1682	75	1542	140	46
1969/1964		1824		
2249/2244		2104		
2529/2524		2384		
2809/2804		2664		



VERTICAL CORNER (SIDE VIEW)

REBA 50 Line VRT CORNER				
L	A	B	C	E
606	141	405	130	42


REBA 65 Line VRT CORNER				
L	A	B	C	E
606	141	405	130	42




HORIZONTAL CORNER (TOP VIEW)

REBA 50 Line HRZ CORNER				
L	A	B	C	E
608	141	380	125	42


REBA 65 Line HRZ CORNER				
L	A	B	C	E
608	141	380	125	42



1



2



FOR SUSPENDED VERSION READ:
POUR LA VERSION SUSPENDUE LIRE:
FÜR DIE HÄNGEVERSION BITTE LESEN SIE:
PARA VERSÃO SUSPENDIDA LEER:




IIV652

3


1.

x2




2.

x2




3.




4


1.







2.




3.





9




FOR LED MODULE PLEASE READ:
POUR PROFILÉ INTÉRIEUR LED LIRE:
FÜR INNEN LED PROFIL BITTE LESEN SIE:
PARA MÓDULO INTERIOR LED LER:
PARA PERFIL INTERIOR LED LEER:




IIV662 or/ou/
odet/
IIV910 ou/o

10


1.



2.




3.



11

1.



2.

